

- NOTES:
1. MATERIAL: COPPER C1100, TIN PLATED
  2. UNLESS OTHERWISE NOTED, BURR SHALL NOT EXCEED 10% OF THE RAW MATERIAL THICKNESS AT ANY LOCATION
  3. PART TO BE CLEAN, DEGREASED, FREE OF CONTAMINATION


UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.



DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE



DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
COPIES TO		MATERIAL SPEC			
1	9	18	SEE NOTE		
2	10	19	FINISH		
3	12	20	SEE NOTE		
4	13	21	DATE	06/26/13	SCALE
5	14	23	FYUE		SUPER DR
6	15	33	CHK		FINISH GOOD WT
7	16	43	APPD		GRAMS/PIECE
8	17	53			
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)					
DIMENSION	0.5 - 3	UP TO OVER	3 - 6	UP TO OVER	30 - 120
TOLERANCE	+0.05	±0.05	±0.1	±0.15	±0.2
3RD ANGLE PROJECTION					
TITLE 5 POSITION BUS BAR					
- FLEX MIDI HOLDER					
REVISION					DRWG. NO.
B					OL-882-267-005

