


**SP1212****12A Discrete Unidirectional TVS Diode****OBSOLETE** DATE: 9/30/2021 PCN/ECN# ESU270-62  
REPLACED BY: SP1250-01ETG**Description**

The SP1212 unidirectional TVS is fabricated in a proprietary silicon avalanche technology. These diodes provide a high ESD (electrostatic discharge) protection level for electronic equipment. The SP1212 TVS can safely absorb repetitive ESD strikes of  $\pm 30$  kV (contact and air discharge as defined in IEC 61000-4-2) without any performance degradation. Additionally, each TVS can safely dissipate a 12A 8/20 surge event as defined in IEC 61000-4-5 2nd Edition.

**Features & Benefits**

- ESD, IEC 61000-4-2,  $\pm 30$ kV contact,  $\pm 30$ kV air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Lightning, 12A (8/20 $\mu$ s as defined in IEC 61000-4-5 2nd edition)
- AEC-Q101 qualified
- Lead free and RoHS compliant
- Moisture Sensitivity Level(MSL -1)

**Additional Information**


Resources



Accessories



Samples

**Pinout and Functional Block Diagram****Applications**

- Switches / Buttons
- Test Equipment / Instrumentation
- Point-of-Sale Terminals
- Medical Equipment
- Notebooks / Desktops / Servers
- Computer Peripherals
- Battery

Life Support Note:

**Not Intended for Use in Life Support or Life Saving Applications**

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

**SP1212****12A Discrete Unidirectional TVS Diode****Absolute Maximum Ratings**

Symbol	Parameter	Value	Units
$P_{pk}$	Peak Pulse Power ( $t_p=8/20\mu s$ )	250	W
$T_{OP}$	Operating Temperature	-40 to 125	°C
$T_{STOR}$	Storage Temperature	-55 to 150	°C



**Caution:** Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

**Electrical Characteristics ( $T_{OP}=25^\circ C$ )**

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	$V_{RWM}$	$I_R=1\mu A$			5.0	V
Breakdown Voltage	$V_{BR}$	$I_R=1mA$		7.0		V
Reverse Leakage Current	$I_{LEAK}$	$V_R=5V$		0.1	0.5	$\mu A$
Clamp Voltage <sup>1</sup>	$V_C$	$I_{PP}=1A, t_p=8/20\mu s$		7.5		V
		$I_{PP}=12A, t_p=8/20\mu s$		9.7		V
Dynamic Resistance <sup>2</sup>	$R_{DYN}$	TLP, $t_p=100ns$ , I/O to GND		0.33		$\Omega$
Peak Pulse Current	$I_{PP}$	$t_p=8/20\mu s$		12		A
ESD Withstand Voltage <sup>1</sup>	$V_{ESD}$	IEC 61000-4-2 (Contact Discharge)	$\pm 30$			kV
		IEC 61000-4-2 (Air Discharge)	$\pm 30$			kV
Diode Capacitance <sup>1</sup>	$C_{I/O-GND}$	Reverse Bias=0V, $f=1MHz$		290		pF

**Note:**


- Parameter is guaranteed by design and/or component characterization.
- Transmission Line Pulse (TLP) with 100ns width, 2ns rise time, and average window  $t_1=70ns$  to  $t_2=90ns$

**8/20 $\mu s$  Pulse Waveform****Clamping Voltage vs IPP for 8/20 $\mu s$  waveshape**


# SP1212

## 12A Discrete Unidirectional TVS Diode


Capacitance vs. Bias




Positive Transmission Line Pulsing (TLP) Plot




Negative Transmission Line Pulsing (TLP) Plot



IEC 61000-4-2 +8 kV Contact ESD Clamping Voltage



IEC 61000-4-2 -8 kV Contact ESD Clamping Voltage



# SP1212

## 12A Discrete Unidirectional TVS Diode


### Soldering Parameters

<b>Reflow Condition</b>		Pb – Free assembly
<b>Pre Heat</b>	- Temperature Min ( $T_{s(min)}$ )	150°C
	- Temperature Max ( $T_{s(max)}$ )	200°C
	- Time (min to max) ( $t_s$ )	60 – 180 secs
<b>Average ramp up rate (Liquidus) Temp (<math>T_L</math>) to peak</b>		3°C/second max
<b><math>T_{s(max)}</math> to <math>T_L</math> - Ramp-up Rate</b>		3°C/second max
<b>Reflow</b>	- Temperature ( $T_L$ ) (Liquidus)	217°C
	- Temperature ( $t_L$ )	60 – 150 seconds
<b>Peak Temperature (<math>T_p</math>)</b>		260 <sup>+0/-5</sup> °C
<b>Time within 5°C of actual peak Temperature (<math>t_p</math>)</b>		20 – 40 seconds
<b>Ramp-down Rate</b>		6°C/second max
<b>Time 25°C to peak Temperature (<math>T_p</math>)</b>		8 minutes Max.
<b>Do not exceed</b>		260°C

### Ordering Information



Part Number	Package	Min. Order Qty.
SP1212-01ETG	SOD882	10000

### Part Marking System




F = Part Code  
\* = Date Code

### Part Numbering System




### Product Characteristics

<b>Lead Plating</b>	Matte Tin
<b>Lead Material</b>	Copper Alloy
<b>Substrate Material</b>	Silicon
<b>Body Material</b>	Molded Compound
<b>Flammability</b>	UL Recognized compound meeting flammability rating V-0

**SP1212****12A Discrete Unidirectional TVS Diode****Package Dimensions — SOD882**

Drawing#: E01-A

Symbol	Package	SOD882				
	JEDEC	MO-236				
	Millimeters			Inches		
	Min	Typ	Max	Min	Typ	Max
<b>A</b>	0.50	0.55	0.60	0.020	0.022	0.024
<b>A1</b>	0.00	0.02	0.05	0.000	0.001	0.002
<b>L1</b>	0.20	0.25	0.30	0.008	0.010	0.012
<b>L2</b>	0.45	0.50	0.55	0.018	0.020	0.022
<b>D</b>	0.90	1.00	1.10	0.035	0.039	0.043
<b>E</b>	0.50	0.60	0.70	0.020	0.024	0.028
<b>e</b>	0.65 BSC			0.026 BSC		
<b>h</b>	0.125 ( x 45° )			0.005 ( x 45° )		

**Embossed Carrier Tape & Reel Specification — SOD882**

Symbol	Tape Dimensions	
	Millimeters	
	Min	Max
<b>A0</b>	0.65	0.75
<b>B0</b>	1.10	1.20
<b>K0</b>	0.50	0.60
<b>E</b>	1.65	1.85
<b>F</b>	3.45	3.55
<b>P0</b>	3.90	4.10
<b>P1</b>	1.90	2.10
<b>P2</b>	1.95	2.05
<b>T</b>	1.95	2.05
<b>W</b>	7.90	8.10

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.