

8 7 6 5 4 3 2 1

THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

ITEM	DESCRIPTION	PART NUMBER
A	2-POSITION	882-869-2
B	3-POSITION	882-869-3
C	4-POSITION	882-869-4
D	5-POSITION	882-869-5
E	6-POSITION	882-869-6
F	7-POSITION	882-869-7

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300103. INITIAL RELEASE. DSILVA	10/4/2022	L.ARGIL

(7X) Ø 10.5 THRU

23.8

11.9

13.5

32 TYP

59 FOR 2-POSITION ONLY

91 FOR 3-POSITION ONLY

123 FOR 4-POSITION ONLY

155 FOR 5-POSITION ONLY

187 FOR 6-POSITION ONLY

219 FOR 7-POSITION ONLY

SCALE 1:2

2.00

NOTES:
1. MATERIAL: COPPER, TIN PLATED.

NO.	COMPONENT NO.	COMPONENT NAME	QTY	U	
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)					
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400	ANGLE
±0.05	±0.05	±0.10	±0.15	±0.20	NONE

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

PER CHI-NPD20-0008 PROCEDURE	SYMBOL	DESCRIPTION
	●	FIT/ FUNCTION CRITICAL CHARACTERISTICS
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
	(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NAME	DATE	<p>Littelfuse Expertise Applied Answers Delivered</p>	TITLE	
DRAWN DSILVA	9/12/2022			BUS BAR FOR ZCASE FUSE BOX
CHECKED -	-			
-	-			
-	-			
FORM NO: CVP-PE40-0003 REV B		SIZE	DWG. NO.	
THIRD ANGLE PROJECTION		B	OL-882-869-0	
DO NOT SCALE DRAWING		SCALE 1:1	REV. A	
			SHEET 1 OF 1	

8 7 6 5 4 3 2 1