


NOTE:  
 1. MATERIAL: C2300 BRASS T-0.35mm, TIN PLATED  
 2. EVERY REEL QUANTITY: 2000 ± 10PCS (ROLL BAND)

UNLESS OTHERWISE SPECIFIED  
 DIMENSIONS ARE IN MILLIMETERS.  
 TOLERANCE  
 DECIMALS ANGULAR  
 X ± 0.25 ± 1°  
 XX ± 0.13  
 DO NOT SCALE DRAWING



METRIC  
 COMPONENT

LITTELFUSE PART NO.	REELED	REVERSE REEL	WIRE GAGE	INTERLEAF	GRIP TYPE			
					A	B	C	D
913-007	YES	NO	10	YES	5.08	5.08	7.11	6.10
913-007-R	YES	YES	10	YES	5.08	5.08	7.11	6.10
913-007-001	NO	NO	10	NO	5.08	5.08	7.11	6.10
913-008	YES	NO	14	YES	4.06	4.06	5.33	4.83
913-008-R	YES	YES	14	YES	4.06	4.06	5.33	4.83
913-008-001	NO	NO	14	NO	4.06	4.06	5.33	4.83

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

COPIES TO		MATERIAL SPEC		SEE NOTE	
1	9	FINISH	SEE NOTE	SCALE	2:1
2	10	DRW	EJIN	DATE	12/12/11
3	12	CHK		DATE	SUPER DR
4	13	APPD		DATE	FINISH GOOD WT
5	14	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)			
6	15	UP TO	OVER	UP TO	OVER
7	16	0.5 - 3	3 - 6	6 - 30	30 - 120
8	17	DIMENSION			
9	18	TOLERANCE			
10	19	3RD ANGLE PROJECTION			
11	20	TITLE			
12	21	CRIMP TERMINAL WITH INSULATION GRIP			
13	22	REVISION			
14	23	DRWG. NO.			
15	24	OL-913-007			
16	25	OUTLINE			