





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

| REVISIONS | | | | |
|-----------|------|--|------------|----------|
| ZONE | REV. | DESCRIPTION | DATE | APPROVED |
| | A | PCO #5300320. INITIAL RELEASE. DSILVA. | 07/18/2023 | E.FLORES |



NOTES:

1.- MATERIAL:

- 1.1.- HOUSING: UL 94V-0 30% GFPA6
- 1.2.- COVER: UL 94V-0 30% GF-PET
- 1.3.- COVER GASKET: SILICON RUBBER

2.- OPERATING TEMPERATURE RANGE: -40 C TO +85 C


3.- FLEC MATES WITH DELPHI GT SERIES 150 AND 280 CONNECTORS

4.- TORQUE M8 NUTS TO 12-18 NM (8.9-13.3 FT.LB)

5.- OPTIONAL TETHER TO BE INSTALLED IN COVER AND ATTACHED TO MOUNTING HOLE BOLT

| ITEM NO. | PART NUMBER | DESCRIPTION | QTY. | U/M |
|---|---|-------------------|----------------|-----|
| DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSIA/SME Y14.5-1994. | | | | |
| ● | FIT/ FUNCTION CRITICAL CHARACTERISTICS | | | |
| <S> | SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL | | | |
| CPK | DENOTES CPK DIMENSIONS MINIMUM CPK VALUE | | | |
| (ST) | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS | | | |
| CP | DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE | | | |
| DRAWN | | NAME | DATE | |
| CHECKED | | D.SILVA | 6/13/2023 | |
| FORM NO. CVP-PE40-0005 REV B | | | | |
| THIRD ANGLE PROJECTION | | | | |
| DO NOT SCALE DRAWING | | SCALE 1:2 | | |
| TITLE | | FLEC MARKET BLANK | | |
| SIZE | DWG. NO. | REV. | | |
| C | OUTLINE | A | OL-FLEC3000Z-0 | |
| SHEET 1 OF 3 | | | | |





| J9 | | |
|---------|---|---|
| R14-87a | H | S |
| F17 | G | R |
| R7-87a | F | P |
| R15-87a | E | N |
| R2-87a | D | M |
| R4-87a | C | L |
| R2-87 | B | K |
| R3-87 | A | J |

| J8 | | |
|--------|---|---|
| F25 | D | H |
| R4-87 | C | G |
| F26 | B | F |
| R6-87a | A | E |

| J7 | | |
|--------|---|---|
| R1-86 | F | M |
| R14-86 | E | L |
| R3-86 | D | K |
| R4-86 | C | J |
| F18 | B | H |
| R17-86 | A | G |

| J4 | | |
|---------|---|---|
| R13-87a | H | A |
| R16-87a | J | B |
| R12-87a | K | C |
| R11-87a | L | D |
| R10-87a | M | E |
| R9-87 | N | F |
| R9-87a | P | G |

| J5 | | |
|--------|---|---|
| R12-86 | J | A |
| R11-86 | K | B |
| R10-86 | L | C |
| F20 | M | D |
| F23 | N | E |
| F27 | P | F |
| F28 | R | G |
| F24 | S | H |

| J6 | | |
|---------|---|---|
| R18-30 | F | A |
| R17-30 | G | B |
| R18-87a | H | C |
| R17-85 | J | D |
| R7-86 | K | E |

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

| | |
|------|---|
| ● | FTI/ FUNCTION CRITICAL CHARACTERISTICS |
| <S> | SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL |
| CPK | DENOTES CPK DIMENSIONS MINIMUM CPK VALUE |
| (ST) | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS |
| CP | DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE |

| | |
|---------------|-----------|
| NAME | DATE |
| DRAWN D.SILVA | 6/13/2023 |
| CHECKED | |
| | |

FORM NO. CVP-PE40-0005 REV B
THIRD ANGLE PROJECTION


Littelfuse
Expertise Applied | Answers Delivered


TITLE: FLEC MARKET BLANK

SIZE: C DWG. NO. OL-FLEC3000Z-0 REV. A
SCALE: 1:1

DO NOT SCALE DRAWING

THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.



| | | |
|---|-----------|---|
| DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSIA/SME Y14.5-1994. | | |
| PER CH-NPDD-008 PROCEDURE | ● | FTI/ FUNCTION CRITICAL CHARACTERISTICS |
| | <S> | SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL |
| | CPK | DENOTES CPK DIMENSIONS MINIMUM CPK VALUE |
| | (ST) | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS |
| | CP | DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE |
| NAME | DATE |  Expertise Applied Answers Delivered |
| DRAWN D.SILVA | 6/13/2023 | |
| CHECKED - | - | |
| - | - | |
| FORM NO. CVP-PE40-0005 REV B | | TITLE |
| THIRD ANGLE PROJECTION | | FLEC MARKET BLANK |
| DO NOT SCALE DRAWING | SCALE 1:1 | SIZE C DWG. NO. OL-FLEC3000Z-0 OUTLINE REV. A |
| | | SHEET 3 OF 3 |