



REVISION		
REV	DATE	DESCRIPTION
A	8/23/2011	50310SERP - RELEASE MRY
B	7/18/2012	505447ECP/C-CHG - REPLACE BASE WITH CURRENT DESIGN -TV
C	12/20/2012	507000ECP - ADD DIMS AND THREAD CALLOUT -TV



**SPECIFICATIONS:**

- VOLTAGE RATING:** 1000VDC
- AMPERE RATING:** 450 AMPERES
- INTERRUPT RATING:** 20kA
- TERMINAL TYPE:** STUD
- TERMINAL TORQUE:** 33.9 N-m (300 in-lb)
- FUSE TORQUE:** 33.9 N-m (300 in-lb)
- APPROVALS:** UL LISTED (UL 4248-18)

●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE. MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

MATL SPEC	FINISH		
DRW TVESELSK	DATE 8/23/2011	SCALE NTS	FINISH GOOD WT GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE PROJECTION	
----------------------	--

**TITLE** LFJ104501STST OUTLINE

<b>Littelfuse</b> CHICAGO, ILLINOIS 60631	REVISION C	DRWG NO. OL-LFJ104501STST	SHEET 1 OF 1
--	------------	---------------------------	--------------