



# SP3130E-01WTG

28 V, 0.3 pF, 30 kV, WLCSP0201, Bidirectional TVS, Ultra Low Capacitance ESD Protection

HF RoHS Pb



## Pinout



## Functional Block Diagram



## Description

The SP3130E-01WTG provides ultra-low capacitance, bidirectional and a high level of protection for electronic equipment that may experience destructive electrostatic discharges (ESD). The typical capacitance of 0.3 pF helps ensure excellent signal integrity on the most challenging consumer electronics interfaces.

It can safely absorb repetitive ESD strikes at  $\pm 30$  kV (contact discharge, IEC 61000-4-2) without performance degradation and safely dissipate 3.0 A of 8/20  $\mu$ s surge current (IEC 61000-4-5 2<sup>nd</sup> edition).

## Features

- ESD, IEC 61000-4-2,  $\pm 30$  kV contact/air
- EFT, IEC 61000-4-4, 40 A (5/50 ns)
- Maximum surge tolerance, IEC 61000-4-5 2<sup>nd</sup> edition, 3.0 A (8/20  $\mu$ s)
- Ultra low capacitance of 0.3 pF (Typ @  $V_R = 0$  V)
- Low leakage current of 1 nA (Typ) at 28 V
- Halogen-free, lead-free and RoHS compliant
- Moisture Sensitivity Level (MSL-1)

## Applications

- USB 2.0, USB 3.0
- Near Field Communications
- RF Signal ESD Protection
- RF Switching, Power Amplifier and Antenna ESD Protection

### Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

# SP3130E-01WTG

## 28 V, 0.3 pF, 30 kV, WLCSP0201, Bidirectional TVS, Ultra Low Capacitance ESD Protection

### Absolute Maximum Ratings

| Symbol     | Parameter                                 | Value      | Units |
|------------|-------------------------------------------|------------|-------|
| $I_{PP}$   | Peak Current ( $t_p = 8/20 \mu\text{s}$ ) | 3.0        | A     |
| $T_{OP}$   | Operating Temperature                     | -40 to 125 | °C    |
| $T_{STOR}$ | Storage Temperature                       | -55 to 150 | °C    |



**CAUTION:** Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

### Electrical Characteristics ( $T_{OP} = 25 \text{ }^\circ\text{C}$ )

| Parameter                            | Symbol       | Test Conditions                                                | Min      | Typ  | Max  | Units    |
|--------------------------------------|--------------|----------------------------------------------------------------|----------|------|------|----------|
| Reverse Standoff Voltage             | $V_{RWM}$    |                                                                |          |      | 28   | V        |
| Breakdown Voltage                    | $V_{BR}$     | $I_R = 1 \text{ mA}$                                           | 30       | 35   | 40   | V        |
| Reverse Leakage Current              | $I_{LEAK}$   | $V_R = 28 \text{ V}$                                           |          | 1    | 50   | nA       |
| Clamp Voltage <sup>1</sup>           | $V_C$        | $I_{PP} = 1 \text{ A}$ , $t_p = 8/20 \mu\text{s}$ , I/O to GND |          | 39   | 44   | V        |
|                                      |              | $I_{PP} = 3 \text{ A}$ , $t_p = 8/20 \mu\text{s}$ , I/O to GND |          | 42   | 48   | V        |
| Dynamic Resistance <sup>1,2</sup>    | $R_{DYN}$    | TLP, $t_p = 100 \text{ ns}$ , I/O to GND                       |          | 0.65 |      | $\Omega$ |
| ESD Withstand Voltage <sup>1,3</sup> | $V_{ESD}$    | IEC 61000-4-2 (Contact Discharge)                              | $\pm 30$ |      |      | kV       |
|                                      |              | IEC 61000-4-2 (Air Discharge)                                  | $\pm 30$ |      |      | kV       |
| Diode Capacitance <sup>1</sup>       | $C_{IO-GND}$ | Reverse Bias = 0 V, $f = 1 \text{ MHz}$ , I/O to GND           |          | 0.30 | 0.45 | pF       |

**Note:**


- Parameter is guaranteed by design and/or component characterization.
- Transmission Line Pulse (TLP) with 100ns width, 0.2 ns rise time, and average window  $t_1 = 70 \text{ ns}$  to  $t_2 = 90 \text{ ns}$
- Device stressed with ten non-repetitive ESD pulses.

**Capacitance vs. Reverse Bias****Clamping Voltage vs  $I_{PP}$** 


**SP3130E-01WTG**

28 V, 0.3 pF, 30 kV, WLCSP0201, Bidirectional TVS, Ultra Low Capacitance ESD Protection


Positive Transmission Line Pulsing (TLP) Plot




Negative Transmission Line Pulsing (TLP) Plot



IEC 61000-4-2 +8 kV Contact ESD Clamping Voltage



IEC 61000-4-2 -8 kV Contact ESD Clamping Voltage



# SP3130E-01WTG

28 V, 0.3 pF, 30 kV, WLCSP0201, Bidirectional TVS, Ultra Low Capacitance ESD Protection


## Soldering Parameters

|                                                                        |                                    |                         |
|------------------------------------------------------------------------|------------------------------------|-------------------------|
| <b>Reflow Condition</b>                                                |                                    | Pb – Free assembly      |
| <b>Pre Heat</b>                                                        | - Temperature Min ( $T_{s(min)}$ ) | 150 °C                  |
|                                                                        | - Temperature Max ( $T_{s(max)}$ ) | 200 °C                  |
|                                                                        | - Time (min to max) ( $t_s$ )      | 60 – 120 seconds        |
| <b>Average Ramp up Rate (Liquidus) Temp (<math>T_L</math>) to Peak</b> |                                    | 3 °C/second max         |
| <b><math>T_{s(max)}</math> to <math>T_L</math> - Ramp-up Rate</b>      |                                    | 3 °C/second max         |
| <b>Reflow</b>                                                          | - Temperature ( $T_L$ ) (Liquidus) | 217 °C                  |
|                                                                        | - Temperature ( $t_L$ )            | 60 – 150 seconds        |
| <b>Peak Temperature (<math>T_p</math>)</b>                             |                                    | 260 <sup>+0/-5</sup> °C |
| <b>Time within 5 °C of Actual Peak Temperature (<math>t_p</math>)</b>  |                                    | 30 seconds              |
| <b>Ramp-down Rate</b>                                                  |                                    | 6 °C/second max         |
| <b>Time 25 °C to Peak Temperature (<math>T_p</math>)</b>               |                                    | 8 minutes max           |
| <b>Do not exceed</b>                                                   |                                    | 260 °C                  |

## Ordering Information

| Part Number   | Package   | Min. Order Qty. |
|---------------|-----------|-----------------|
| SP3130E-01WTG | WLCSP0201 | 10,000          |


## Part Marking System



## Product Characteristics

|                      |                                                        |
|----------------------|--------------------------------------------------------|
| <b>Lead plating</b>  | Tin plating                                            |
| <b>Lead material</b> | Copper bump                                            |
| <b>Flammability</b>  | UL recognized compound meeting flammability rating V-0 |


## Part Numbering System



# SP3130E-01WTG


## 28 V, 0.3 pF, 30 kV, WLCSP0201, Bidirectional TVS, Ultra Low Capacitance ESD Protection

### Package Dimensions — WLCSP0201



| Symbol | Millimeters |       | Inches     |        |
|--------|-------------|-------|------------|--------|
|        | Min         | Max   | Min        | Max    |
| D      | 0.605       | 0.655 | 0.0238     | 0.0258 |
| E      | 0.305       | 0.355 | 0.0120     | 0.0140 |
| D1     | 0.145       | 0.155 | 0.0057     | 0.0061 |
| E1     | 0.245       | 0.255 | 0.0096     | 0.0100 |
| D2     | 0.400 BSC   |       | 0.0157 BSC |        |
| A      | 0.273       | 0.329 | 0.0107     | 0.0130 |
| A2     | 0.265       | 0.315 | 0.0104     | 0.0124 |
| A1     | 0.008       | 0.014 | 0.0003     | 0.0006 |

### Embossed Carrier Tape & Reel Specification — WLCSP0201



| Symbol | Millimeters     |
|--------|-----------------|
| A0     | 0.41+/-0.03     |
| B0     | 0.70+/-0.03     |
| D      | ∅ 1.50 + 0.10   |
| D1     | ∅ 0.20 +/- 0.05 |
| E      | 1.75+/-0.10     |
| F      | 3.50+/-0.05     |
| K0     | 0.38+/-0.03     |
| P0     | 4.00+/-0.10     |
| P1     | 2.00+/-0.05     |
| P2     | 2.00+/-0.05     |
| W      | 8.00+0.30/-0.10 |
| T      | 0.23+/-0.02     |

**Product Disclaimer:** Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. "Littelfuse" includes Littelfuse, Inc., and all of its affiliate entities. <http://www.littelfuse.com/disclaimer-electronics>.