



NOTES :

1. FUSEHOLDER IS SPLASHED-WATERPROOF ACCORDING TO CLASS IP-64 AS DEFINED IN DIN 40050 BLATT 9 DATE FEB. 1975.

METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
◎	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

LTR	DATE	REVISION	CHK	APD
A	03/20/09	00636ER-RELEASE GMB		
B	06/23/11	502726ECA-REDRAWN BASED FROM AVAILABLE 3D MODEL. CORRECTED REFERENCE POSITION OF DIM 66.5mm. RLDJ		
C	7/15/11	502842ECA-UPDATE DRAWING BASED ON ACTUAL PART SUPPLIED TO MARKET. ADD RIB ON LATCH AREA AND CHAMFER ON MAXI BLADE LEG OPENING.		

COPIES TO	MATL SPEC	
1 9 18	PA66 GF 30%	
2 10 19	FINISH	
3 12 20	DRW	RLDJ
4 13 21	DATE	06/23/11
5 14 23	CHK	DATE
6 15 33	APPD	DATE
7 16 43	FINISH GOOD WT	
8 17 53	GRAMS/PIECE	
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fH)		
DIMENSION	0.5 - 3	3 - 6
TOLERANCE	±0.05	±0.05
3RD ANGLE PROJECTION		
TITLE		
SPLASH-PROOF		
MAXI FUSEHOLDER		
REVISION		
C		
DRWG. NO.		
OL-01520003U		

