



- NOTES:
 1. MATERIAL: COPPER C1100, TIN PLATED
 2. UNLESS OTHERWISE NOTED, BURR SHALL NOT EXCEED 10% OF THE RAW MATERIAL THICKNESS AT ANY LOCATION
 3. PART TO BE CLEAN, DEGREASED, FREE OF CONTAMINATION

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙ DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				

LTR	DATE	REVISION	CHK	APD	COPIES TO	MATL SPEC	SEE NOTE		
						FINISH	SEE NOTE		
A	06/26/13	50B674ERA-RELEASE	FYUE		1 9 18	DRW	DATE 06/26/13	SCALE	2:1
B	07/10/13	50B881ECA-THICKNESS 2.3 WAS 2.0	FYUE		2 10 19	CHK	DATE	SUPER DR	
					3 12 20	APPD	DATE	FINISH GOOD WT	
					4 13 21	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)			
					5 14 23	DIMENSION			
					6 15 33	TOLERANCE			
					7 16 43	3RD ANGLE PROJECTION			
					8 17 53	TITLE 2 POSITION BUS BAR			
						- FLEX MIDI HOLDER			
						REVISION			
						DRWG. NO.			
						OL-882-267-002			

