



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY
2. MATERIAL: BODY -- MAPEX UL94 -V0, BLACK
M8 x 1.25 STUD -- SAE1215/DIN 95Mn28/11SMn30 STEEL, ZINC PLATED
3. MAXIMUM MOUNTING TORQUE FOR M4 MOUNTING HOLES 10 N*M, 7.4 LBF*FT
4. MAXIMUM TORQUE FOR M8 STUD 8.9-13.3 LBF*FT, 12-18 N*m

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙ DENOTES CRITICAL CHARACTERISTICS.
CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

2	STUD	1	EA
1	BODY	1	EA
NO	COMPONENT NO	DESCRIPTION	QTY/M

BILL OF MATERIAL

COPIES TO		MATERIAL SPEC		SEE NOTE 2	
1	9	18	FINISH		
2	10	19	SCALE		
3	12	20	DATE	03/21/12	1 : 1
4	13	21	PVN	DATE	SUPER DR
5	14	23	CHK	DATE	FINISH GOOD WT
6	15	33	APPD	DATE	GRAMS/PIECE
7	16	43	TOLERANCES UNLESS OTHERWISE SPECIFIED		
8	17	53	DIMENSION		
			UP TO	OVER	UP TO
			0.5 - 3	6 - 30	120 - 400
			±0.1	±0.2	±0.3
			±0.1	±0.2	±0.5

TITLE		JUNCTION BLOCK	
3RD ANGLE PROJECTION		NON-FEED-THRU	
REVISION		DRWG. NO.	
B		OL-JBPT5N01ZXB	