

# SMF3.3

## Surface Mount – 200W



### Description

SMF3.3 is designed specifically to protect sensitive electronic equipment from voltage transients induced by lightning and other transient voltage events.

### Features and Benefits

- 200W peak pulse power capability at 10/1000 $\mu$ s waveform, repetition rate (duty cycle): 0.01%
- 1200W peak pulse power capability at 8/20 $\mu$ s waveform
- Excellent clamping capability
- Compatible with industrial standard package SOD-123FL
- Low profile: maximum height of 1.08mm.
- For surface mounted applications to optimize board space
- Typical failure mode is short from over-specified voltage or current
- Whisker test is conducted based on JEDEC JESD201A per its table 4a and 4c
- IEC 61000-4-2 ESD 30kV(Air), 30kV (Contact)
- ESD protection of data lines in accordance with IEC 61000-4-2
- EFT protection of data lines in accordance with IEC 61000-4-4
- Fast response time: typically less than 1.0ns from 0 Volts to VBR min
- High temperature soldering: 260°C/30 seconds at terminals
- Built-in strain relief
- Meet MSL level1, per J-STD-020C, LF maximum peak of 260°C
- Matte tin lead-free plated
- Halogen-free and RoHS-compliant
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin(Sn) (IPC/JEDEC J-STD-609A.01)

### Additional Information



Resources



Accessories



Samples

### Agency Approvals

Agency	Agency File Number
	E230531

### Maximum Ratings and Thermal Characteristics

( $T_A=25^\circ\text{C}$  unless otherwise noted)

Parameter	Symbol	Value	Unit
Peak Pulse Power Dissipation at $T_A=25^\circ\text{C}$ (Note 1)	$P_{PPM}$	1200	W
8/20 $\mu$ s (Note 2) 10/1000 $\mu$ s (Note 3)		200	W
Thermal Resistance Junction- to- Ambient	$R_{\theta JA}$	220	$^\circ\text{C/W}$
Thermal Resistance Junction- to- Lead	$R_{\theta JL}$	100	$^\circ\text{C/W}$
Operating Temperature Range	$T_J$	-55 to 150	$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-55 to 150	$^\circ\text{C}$


#### Notes:

1. Non-repetitive current pulse, per Fig. 4 and derated above  $T_J$  (initial) =25 $^\circ\text{C}$  per Fig. 3.

### Applications

SMF3.3 series is ideal for the protection of portable electronics/ hard drives, notebooks, VCC busses, POS terminal, SSDs, power supplies, monitors, and vulnerable circuit used in other consumer applications.

### Functional Diagram



### Electrical Characteristics ( $T_A=25^\circ\text{C}$ unless otherwise noted)

Part Number	Marking Code	Breakdown Voltage $V_{BR}$ (Volts) @ $I_T$		Test Current $I_T$ (mA)	Reverse Stand off Voltage $V_R$ (V)	Maximum Reverse Leakage @ $V_R$ $I_R$ ( $\mu\text{A}$ )	Maximum Peak Pulse Current (10/1000 $\mu\text{S}$ ) $I_{PP}$ (A)	Maximum Clamping Voltage @ $I_{PP}$ (10/1000 $\mu\text{S}$ ) $V_C$ (V)	Maximum Peak Pulse Current (8/20 $\mu\text{S}$ ) $I_{PP}$ (A)	Maximum Clamping Voltage @ $I_{PP}$ (8/20 $\mu\text{S}$ ) $V_C$ (V)
		MIN	MAX							
SMF3.3	33	3.4	4.3	10	3.3	0.5	30.0	6.8	120.0	10.0


#### Notes:

- $V_{BR}$  measured after  $I_T$  applied for 300 $\mu\text{s}$ ,  $I_T$  = square wave pulse or equivalent.
- Surge current waveform per 10/1000 $\mu\text{s}$  exponential wave and derated per Fig.2.
- All terms and symbols are consistent with ANSI/IEEE C62.35.
- Surge current waveform per 8/20 $\mu\text{s}$  exponential wave and derated per Fig.6.

# SMF3.3

## Surface Mount – 200W


### I-V Curve Characteristics




- $P_{PPM}$  Peak Pulse Power Dissipation** – Max power dissipation
  - $V_R$  Stand-off Voltage** -- Maximum voltage that can be applied to the TVS without operation
  - $V_{BR}$  Breakdown Voltage** -- Maximum voltage that flows though the TVS at a specified test current ( $I_T$ )
  - $V_C$  Clamping Voltage** -- Peak voltage measured across the TVS at a specified  $I_{ppm}$  (peak impulse current)
  - $I_R$  Reverse Leakage Current** – Current measured at  $V_R$
  - $V_F$  Forward Voltage Drop for Uni-directional**
- Note:**  $V_F$  distribution range from 7V to 16V at  $I_F$  1mA.

### Ratings and Characteristic Curves ( $T_A=25^\circ C$ unless otherwise noted)


**Figure 1 -**  
TVS Transients Clamping Waveform




**Figure 2 -**  
Peak Pulse Power Rating Curve



**Figure 3 -**  
Peak Pulse Power Derating Curve




**Figure 4 -**  
10/1000 $\mu$ S Pulse Waveform




# SMF3.3

## Surface Mount – 200W

**Figure 5 -**  
Capacitance vs. Reverse Bias




**Figure 6 -**  
8/20 $\mu$ S Pulse Waveform



## Soldering Parameters

<b>Reflow Condition</b>		Lead-free assembly
<b>Pre Heat</b>	- Temperature Min ( $T_{s(min)}$ )	150°C
	- Temperature Max ( $T_{s(max)}$ )	200°C
	- Time (min to max) ( $t_s$ )	60 – 120 secs
<b>Average ramp up rate (Liquidus Temp (<math>T_L</math>) to peak)</b>		3°C/second max
<b><math>T_{s(max)}</math> to <math>T_L</math> - Ramp-up Rate</b>		3°C/second max
<b>Reflow</b>	- Temperature ( $T_L$ ) (Liquidus)	217°C
	- Time (min to max) ( $t_r$ )	60 – 150 seconds
<b>Peak Temperature (<math>T_p</math>)</b>		260 <sup>+0/-5</sup> °C
<b>Time within 5°C of actual peak Temperature (<math>t_p</math>)</b>		30 seconds max
<b>Ramp-down Rate</b>		6°C/second max
<b>Time 25°C to peak Temperature (<math>T_p</math>)</b>		8 minutes max.
<b>Do not exceed</b>		260°C



## Physical Specifications

<b>Case</b>	SOD-123FL plastic over passivated junction
<b>Polarity</b>	Color band denotes cathode except bipolar
<b>Terminal</b>	Matte tin-plated leads, solderable per JESD22-B102


## Environmental Specification

<b>High Temp. Storage</b>	JESD22-A103
<b>HTRB</b>	JESD22-A108
<b>Temperature Cycling</b>	JESD22-A104
<b>MSL</b>	JEDEC-J-STD-020, LEVEL 1
<b>H3TRB</b>	JESD22-A101
<b>RSH</b>	JESD22-A111

# SMF3.3


## Surface Mount – 200W

### Dimensions - SOD-123FL Package




Dimensions	Millimeters		Inches	
	Min	Max	Min	Max
A	2.70	3.10	0.106	0.122
B	3.50	3.90	0.138	0.154
C	0.85	1.05	0.033	0.041
D	1.70	2.00	0.067	0.079
E	0.43	0.83	0.017	0.033
F	0.10	0.25	0.004	0.010
G	0.00	0.10	0.000	0.004
H	0.90	1.08	0.035	0.043
I	0.00	0.20	0.000	0.008
J	0.40	0.60	0.016	0.024

### Part Numbering System




### Part Marking System



### Packaging Options

Part number	Component Package	Quantity	Packaging Option	Packaging Specification
SMF3.3	SOD-123FL	3000	Tape & Reel – 8mm tape/7" reel	EIA RS-481

### Tape and Reel Specification



**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.