



Ref. Certif. No.

DK-74156-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Voltage Maintained Thermal cut-out

Name and address of the applicant

LITTELFUSE INC
SUITE 500
8755 W HIGGINS RD
CHICAGO, IL 60631 USA

Name and address of the manufacturer

LITTELFUSE INC
SUITE 500
8755 W HIGGINS RD
CHICAGO, IL 60631 USA

Name and address of the factory

LITTELFUSE ELECTRONICS (KUNSHAN) CO., LTD
NO.389 CENTRAL AVE, ZONE B, EPZ KUNSHAN JIANGSU
215312
CHINA

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

Contact: 9 Vdc, 30 A
Load Type: Resistive
Cycles: 6,000
Opening Temperature: 72, 77, 82, 85 or 90 °C

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

TAT18
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 60730-2-9:2010, EN 60730-1:2011;
National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60730-1(ed.4), IEC 60730-2-9(ed.3),
IEC 60730-2-9(ed.3);am1

As shown in the Test Report Ref. No. which forms part of this Certificate

4788061316-20180621 issued on 2018-06-21

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-06-25

Signature:

Jan-Erik Storgaard

Model Details:

TAT18-, ww/o, 9-, f/b 72, 77, 82, 85 or 90

All models may have prefix MHP- and one or more suffixes may be added.

ww/o: with or without

f/b: followed by

Model Nomenclature:

MHP-TAT	18	-	9	-	xx
I	II		III		IV

- | | | |
|-----|---|--|
| I | - | Basic type designation
TAT
May have prefix MHP- |
| II | - | Manufacture Specified Holding Current Rating, (A)
18 |
| III | - | Voltage Rating in DC, (V)
9 |
| IV | - | Depends on space, it is optional
Set point temperature rating, (°C)
72, 77, 82, 85 or 90 |

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-06-25

Signature:

Jan-Erik Storgaard