TOO, TLO, SOO & SLO SERIES PLUG FUSES

125 Vac • ¼-30 A

Description

Littelfuse Plug fuses provide overcurrent protection to general purpose circuits and small motor loads. Edison-base Plug fuses (TOO and TLO series) feature metal threads similar to incandescent lamp bases.

Type S Plug fuses (SOO and SLO series) utilize a nonmetallic threaded base and must be used with Type S adapters (SAO series).

The National Electrical Code permits Edison base Plug fuses to be used for replacement purposes only. Type S fuses and adapters prevent shunting open fuses and over-fusing.

Specifications

Voltage Rating	125 Vac
Interrupting Rating	10 kA rms symmetrical
Approvals	UL Listed 248-11

Web Resources

More information: **littelfuse.com/plug**

Ordering Information

SERIES	AMPERAGE	CATALOG NUMBER	ORDERING NUMBER
TOO	1/4	TOO.250	TOO.250Z
TLO	15	TLO015	TLO015.Z
SOO	2 8/10	SOO02.8	SOO02.8Z
SLO	30	SLO030	SLO030.Z

TOO Series - Dual-element time-delay Edison base fuses

AMPERE RATINGS			
2	1/4	12	25
4	8	15	30
5	10	20	—

TLO Series - Medium time-delay Edison base fuses

AMPERE RATINGS			
15	20	25	30

SOO Series - Dual-element time-delay Type S fuses

AMPERE RATINGS					
1/4	1	2	3 1/2	6 1/4	14
3/10	1 1/8	2 1/4	4	7	15
4/10	1 1/4	2 1/2	4 1/2	8	20
1/2	1 4/10	2 8/10	5	9	25
6/10	1 6/10	3	5 6/10	10	30
8/10	1 8/10	3 2/10	6	12	

SLO Series - Medium time-delay Type S fuses

AMPERE RATINGS			
15	20	25	30

SAO Series - Type S fuse adapters

SAO ADAPTER	ACCEPTS FUSE RATINGS
SAO001	1/4 - 1
SAO1.25	1/4 - 1 1/4
SAO01.6	1/4 - 1 6/10
SAO002	1 8/10 - 2
SAO02.5	1 8/10 - 2 1/2
SAO03.2	1 8/10 - 3 2/10
SAO004	3 1/2 - 4
SAO005	3 1/2 - 5
SAO6.25	3 1/2 - 6 1/4
SAO008	7 - 8
SAO015	7 - 15
SAO020	20 only
SAO030	20 - 30

© 2013 Littelfuse POWR-GARD® Products