


# DSA60C60PB

## 60 V, 60 A Schottky Rectifier Diode

RoHS


Pb



### Features:

- Very low  $V_F$
- Extremely low switching losses
- Low  $I_{RM}$  values
- Improved thermal behavior
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching
- Terminals finish: 100% pure tin
- This is a Pb-free device
- Epoxy meets UL 94 V-0

### Pinout Diagram (TO-220-3L AB)



**C:** Cathode; **A:** Anode; **tab:** Cathode

### Applications:

- Rectifiers in Switch Mode Power Supplies (SMPS)
- Free wheeling diode in low voltage converters

### Product Summary

| Characteristic | Value  | Unit |
|----------------|--------|------|
| $V_{RRM}$      | 60     | V    |
| $I_{FAV}$      | 2 x 30 | A    |
| $V_F$          | 0.77   | V    |

**Maximum Ratings** ( $T_A = 25^\circ\text{C}$  unless otherwise specified)

| Symbol    | Characteristics                                       | Condition  | Max.                            | Units |
|-----------|---|--|---------------------------------|-------|
| $V_{RRM}$ | Peak Repetitive Reverse Voltage                       | -  | 60                              | V     |
| $V_{RWM}$ | Working Peak Reverse Voltage                          |  |                                 |       |
| $V_R$     | DC Blocking Voltage                                   |  |                                 |       |
| $I_{FAV}$ | Average Rectified Forward Current                     | 50% duty cycle @ $T_C = 155^\circ\text{C}$ , rectangular wave form | 30 (Per Leg)<br>60 (Per Device) | A     |
| $I_{FSM}$ | Peak One Cycle Non-Repetitive Surge Current (Per Leg) | 10 ms, Half Sine pulse, $T_{VJ} = 25^\circ\text{C}$                | 340                             | A     |
| $P_{tot}$ | Total power dissipation                               | $T_C = 25^\circ\text{C}$   | 175                             | W     |

**Electrical Characteristics** ( $T_A = 25^\circ\text{C}$  unless otherwise specified)

| Symbol   | Characteristics                             | Conditions  | Typ. | Max. | Units         |
|----------|---|---|------|------|---------------|
| $V_{F1}$ | Forward Voltage Drop (Per Leg) <sup>1</sup> | @ 30 A, Pulse, $T_{VJ} = 25^\circ\text{C}$                                  | -    | 0.92 | V             |
| $V_{F2}$ |   | @ 30 A, Pulse, $T_{VJ} = 125^\circ\text{C}$                                 | -    | 0.77 | V             |
| $I_{R1}$ | Reverse Current (Per Leg) <sup>1</sup>      | @ $V_R = \text{rated } V_R, T_{VJ} = 25^\circ\text{C}$                      | -    | 450  | $\mu\text{A}$ |
| $I_{R2}$ |   | @ $V_R = \text{rated } V_R, T_{VJ} = 125^\circ\text{C}$                     | -    | 5    | mA            |
| $C_T$    | Junction Capacitance (Per Leg)              | @ $V_R = 12 \text{ V}, T_C = 25^\circ\text{C}$<br>$f_{SIG} = 1 \text{ MHz}$ | 410  | -    | pF            |


**Note 1:** Pulse width < 300  $\mu\text{s}$ , duty cycle < 2%

**Thermal-Mechanical Specifications**


| Symbol     | Characteristics                                  | Condition    | Specification      | Units            |
|------------|--|--------------|--------------------|------------------|
| $T_{VJ}$   | Junction Temperature                             | -            | -55 to +175        | $^\circ\text{C}$ |
| $T_O$      | Operation temperature                            | -            | -55 to +150        | $^\circ\text{C}$ |
| $T_{stg}$  | Storage Temperature                              | -            | -55 to +150        | $^\circ\text{C}$ |
| $M_D$      | Mounting torque                                  | -            | Min 0.4<br>Max 0.6 | Nm               |
| $F_C$      | Mounting force with clip                         | -            | Min 20<br>Max 60   | N                |
| $R_{thJC}$ | Maximum Thermal Resistance Junction to Case      | DC operation | 0.85               | K/W              |
| $R_{thJS}$ | Typical Thermal Resistance Junction to Heat Sink | -            | 0.5                | K/W              |
| wt         | Approximate Weight                               | -            | 2                  | g                |

### Characteristic Curves


**Fig. 1. Typical Forward Characteristics**



**Fig. 2. Typical Reverse Characteristics**



**Fig. 3. Typical Junction Capacitance**




Part Outline Drawing (TO-220-3L AB)



| Symbol | Inches |         |       | Millimeters |         |       |
|--------|--------|---------|-------|-------------|---------|-------|
|        | Min.   | Typical | Max.  | Min.        | Typical | Max.  |
| A      | 0.140  | -       | 0.190 | 3.56        | -       | 4.83  |
| A1     | 0.020  | -       | 0.055 | 0.51        | -       | 1.40  |
| A2     | 0.080  | -       | 0.115 | 2.03        | -       | 2.92  |
| b      | 0.015  | -       | 0.040 | 0.38        | -       | 1.02  |
| b1     | 0.045  | -       | 0.070 | 1.14        | -       | 1.78  |
| c      | 0.012  | -       | 0.024 | 0.31        | -       | 0.61  |
| D      | 0.560  | -       | 0.650 | 14.22       | -       | 16.51 |
| D1     | 0.330  | -       | 0.371 | 8.38        | -       | 9.42  |
| E      | 0.380  | -       | 0.420 | 9.65        | -       | 10.67 |
| e      | -      | 0.100   | -     | -           | 2.54    | -     |
| e1     | -      | 0.200   | -     | -           | 5.08    | -     |
| H1     | 0.230  | -       | 0.270 | 5.84        | -       | 6.86  |
| L      | 0.500  | -       | 0.580 | 12.70       | -       | 14.73 |
| L1     | -      | -       | 0.250 | -           | -       | 6.35  |
| ØP     | -      | 0.140   | -     | -           | 3.56    | -     |
| Q      | 0.100  | -       | 0.135 | 2.54        | -       | 3.43  |

Part Number and Marking




- D = Diode
- S = Schottky Diode
- A Low VF
- 60 = Forward Current (60A)
- C Common Cathode
- 60 = Reverse Voltage (60V)
- PB = Package Code (TO-220AB)
- YY = Year
- WW = Work Week
- S = Plant Location Code
- XXXXXXXXXX = Lot Number

Ordering Information

| Part Number | Marking    | Packing Mode | Quantity     |
|-------------|------------|--------------|--------------|
| DSA60C60PB  | DSA60C60PB | Tube         | 50 pcs/ tube |

Packing Specifications



Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

